



3/4 in. Flex to 3/4 in. EMT Squeeze/Compression Coupling

By Raco
Catalog # 1943

3/4 in. Flex to 3/4 in. EMT Squeeze/Compression Coupling



*Representative Image

Features

- Rugged metallic construction ensures mechanical protection
- Steel/malleable components are electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Conduit Type	EMT
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Couplings
Material	Malleable Iron
UPC	050169019436

Dimensions

Dimensions	1.828 in x 1.125 in x 1.75 in
Height	1.75 in
Length	1.828 in
Trade Size	3/4 in Flex to 3/4 in EMT
Weight	0.238 lb
Width	1.125 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1943-SPEC-EN | REV 6/2024