



## 3/4 in. Flex to 3/4 in. EMT Squeeze/Compression Coupling

By Raco  
Catalog # 1943-8



\*Representative Image

3/4 in. Flex to 3/4 in. EMT Squeeze/Compression Coupling

### Features

- Rugged metallic construction ensures mechanical protection
- Steel/malleable components are electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

### General

Conduit Type	EMT
Connector Type	Squeeze
Fitting Type	Couplings
Material	Malleable Iron
UPC	050169194386

### Dimensions

Dimensions	1.828 in x 1.125 in x 1.75 in
Height	1.75 in
Length	1.828 in
Trade Size	3/4 in Flex to 3/4 in EMT
Weight	0.255 lb
Width	1.125 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	6080

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand