



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, FS, Flush Bracket

By Raco
Catalog # 196



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, FS, Flush Bracket

Features

- TKO knockout design provides installation flexibility
- FS style bracket, flush
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

General

Bracket Type	FS, for Metal or Wood Studs
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169901960
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	6.875 in
Raised Ground	No
Weight	0.808 lb
Width	4.375 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 196](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - RACO: 196 Universal Box Bracket Installation Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-196-SPEC-EN | REV 6/2024