



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, FS, Flush Bracket

By RACO
Catalog # 196

4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, FS, Flush Bracket



Features

- TKO knockout design provides installation flexibility
- FS style bracket, flush
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)

Configuration

Knockouts	<ul style="list-style-type: none">• 1/2 in• 1/2 - 3/4 in Combination (TKO)
Bracket Type	FS, for Metal or Wood Studs

Dimensions

Cubic Capacity	21.0 cu.in
----------------	------------

Depth	1.5 in
Size	4 in
Actual Depth	1.563 in
Raised Ground	No
Width	4.375 in
Weight	0.808 lb.
Height	6.875 in

General

Wiring System	Conduit
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Welded
UPC	050169901960

Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	1650

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)