



3/4 in. EMT Set-Screw Connector, Uninsulated

By RACO
Catalog # 2003

3/4 in. EMT Set-Screw Connector, Uninsulated



Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- 1 set-screw

Specifications

Certified Listed	cULus Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Industry Standard(s)	UL 514B
Buy America(n) Qualified	Contact Manufacturer

Configuration

Connector Type	Set-Screw
----------------	-----------

Dimensions

Package Length	6.943 in
Package Width	4.581 in
Package Weight	3.439 lb.

Trade Size	3/4 in
Package Height	4.240 in
Length	1.476 in
Width	1.087 in
Weight	0.138 lb.
Height	1.087 in
Dimensions	1.476 in x 1.087 in x 1.087 in

General

Fitting Type	Connectors
Insulation Type	Uninsulated
Conduit Type	EMT
Material	Steel
UPC	050169020036

Logistics

Minimum Pack Quantity	25
Carton Quantity	250
Pallet Quantity	10000

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)