



## 3/4 in. EMT Set-Screw Connector, Uninsulated

By Raco  
Catalog # 2003

3/4 in. EMT Set-Screw Connector, Uninsulated



\*Representative Image

### Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- 1 set-screw

### General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169020036

### Dimensions

Dimensions	1.476 in x 1.087 in x 1.087 in
Height	1.087 in
Length	1.476 in
Trade Size	3/4 in
Weight	0.138 lb
Width	1.087 in

### Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	250
Minimum Pack Quantity	25
Pallet Quantity	10000

### Product Assets

[Brochures - HCC Products for Solar](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195970 - 2](#)  
[Product Logo - Conduit](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2003-SPEC-EN | REV 6/2024