



2 in. EMT Set-Screw Connector, Uninsulated

By RACO
Catalog # 2008

2 in. EMT Set-Screw Connector, Uninsulated



Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- 2 set-screw

Specifications

Certified Listed	cULus Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Industry Standard(s)	UL 514B
Buy America(n) Qualified	Contact Manufacturer

Configuration

Connector Type	Set-Screw
----------------	-----------

Dimensions

Trade Size	2 in
------------	------

Length	2.88 in
Width	2.75 in
Weight	0.553 lb.
Height	3 in
Dimensions	2.88 in x 2.75 in x 3 in

General

Fitting Type	Connectors
Insulation Type	Uninsulated
Conduit Type	EMT
Material	Steel
UPC	050169020081

Logistics

Minimum Pack Quantity	20
Carton Quantity	20
Pallet Quantity	1800

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)