



2 in. EMT Set-Screw Connector, Uninsulated

By Raco
Catalog # 2008

2 in. EMT Set-Screw Connector, Uninsulated



*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- cULus
- Available in trade sizes of 1/2 in. through 4 in.
- 2 set-screw

General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel
UPC	050169020081

Dimensions

Dimensions	2.88 in x 2.75 in x 3 in
Height	3 in
Length	2.88 in
Trade Size	2 in
Weight	0.553 lb
Width	2.75 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	1800

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 2](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2008-SPEC-EN | REV 6/2024