



Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, 2028FBAR

By Raco
Catalog # 2028FBAR



Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, Flanged with Vapor Barrier

Features

- Self-clamping wire entry clamps
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- Front mounted grounding screw with combination straight/Robertson head

General

Bracket Setback	0.5
Cable Clamps	4
Catalog Number	2028FBAR
Color	Yellow
Material	Thermoplastic Resin
Style	Vapor Barrier
Type	<ul style="list-style-type: none">• Vapor Barrier Box• Box
UPC	805035054536
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Dimensions	6.93 in x 5.118 in x 3.150 in
Fixture Lbs.	50 lb
Height	3.15 in
Length	6.93 in
Weight	.265 lb
Width	5.118 in

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	40
Pallet Quantity	640

Product Assets

- [360 Product View - RACO_2028FBAR](#)
- [3D Product View - 2028FBAR](#)
- [Brochures - Vapor Barrier Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Nonmetallic Cable Boxes](#)
- [Specifications - 2028FBAR](#)