



## #2TS-1/2 in. EMT Threaded Hanger

By Raco  
Catalog # 2041TH

#2TS-1/2 in. EMT Threaded Hanger



\*Representative Image

### Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	2-1/2
Material	Steel
Max Load Lbs.	75 lb
UPC	050169911938

### Dimensions

Dimensions	1.688 in x 0.88 in x 2.84 in
EMT Size	1.25 in
Height	2.84 in
Length	1.688 in
Trade Size	EMT 1-1/4 in
Weight	0.102 lb
Width	0.88 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	7200

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195968-3](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
RACO-2041TH-SPEC-EN | REV 6/2024