



#0TS 0.5 in Rigid/EMT Conduit Hanger

By Raco
Catalog # 2052

#0TS 0.5 in Rigid/EMT Conduit Hanger

Features

- Furnished with nut and bolt to speed installation
- Pregalvanized finish provides corrosion protection
- Additional sizes available

Application

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls

General

Catalog Number	2052
Hanger Size	0
Material	Steel
UPC	050169020524

Dimensions

Dimensions	1.813 in x 0.75 in x 0.781 in
EMT Size	0.5 in
Height	0.781 in
Length	1.813 in
Rigid/IMC Size	0.5 in



*Representative Image

Trade Size	0
Weight	0.082 lb
Width	0.75 in

Certifications And Compliance

Certified Listed	cULus Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	14000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195968-1](#)
[Sales Drawings - 2052 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 2052](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand