



## #OTS 1/2 in. Rigid/EMT Threaded Hanger

By Raco  
Catalog # 2052TH

#OTS 1/2 in. Rigid/EMT Threaded Hanger



\*Representative Image

### Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	0
Material	Steel
Max Load Lbs.	50 lb
UPC	050169911907

### Dimensions

Dimensions	1 in x 0.73 in x 1.98 in
EMT Size	0.5 in
Height	1.98 in
Length	1 in
Rigid/IMC Size	0.5 in
Trade Size	1/2 in
Weight	0.062 lb
Width	0.73 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	15000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195968-3](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2052TH-SPEC-EN | REV 6/2024