



# #1TS 3/4 in. Rigid/EMT Threaded Hanger

By Raco  
Catalog # 2053TH

#1TS 3/4 in. Rigid/EMT Threaded Hanger



\*Representative Image

## Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

## General

Catalog Number	2053TH
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	1
Material	Steel
Max Load Lbs.	50 lb
UPC	050169911914

## Dimensions

Dimensions	1.13 in x 0.72 in x 2.14 in
EMT Size	0.75 in

Height	2.14 in
Length	1.13 in
Rigid/IMC Size	0.75 in
Trade Size	3/4 in
Weight	0.066 lb
Width	0.72 in

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer cULus Listed
--	--------------------------------------

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195968-3](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)
- [Specifications - 2053TH](#)
- [Terms and Conditions - HCC Terms & Conditions](#)