



#2TS 1 in. Rigid/EMT Threaded Hanger

By Raco
Catalog # 2054TH

#2TS 1 in. Rigid/EMT Threaded Hanger

Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

General

Catalog Number	2054TH
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	2
Material	Steel
Max Load Lbs.	60 lb
UPC	050169911921

Dimensions

Dimensions	1.437 in x 0.89 in x 2.48 in
EMT Size	1 in
Height	2.48 in
Length	1.437 in



*Representative Image

Rigid/IMC Size	1 in
Trade Size	1 in
Weight	0.084 lb
Width	0.89 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	9600

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195968-3](#)
- [Certifications - UL COC - E195969-5](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)
- [Specifications - 2054TH](#)
- [Terms and Conditions - HCC Terms & Conditions](#)