



#3TS 1.25 in Rigid, 1.5 in EMT Conduit Hanger

By Raco
Catalog # 2055

#3TS 1.25 in Rigid, 1.5 in EMT Conduit Hanger

Features

- Furnished with nut and bolt to speed installation
- Pregalvanized finish provides corrosion protection
- Additional sizes available

Application

For use in wet or dry locations to support runs of rigid/IMC and EMT conduit from ceilings and walls

General

| | |
|----------------|--------------|
| Catalog Number | 2055 |
| Hanger Size | 3 |
| Material | Steel |
| UPC | 050169020555 |

Dimensions

| | |
|----------------|--------------------------------|
| Dimensions | 2.875 in x 0.875 in x 1.594 in |
| EMT Size | 1.5 in |
| Height | 1.594 in |
| Length | 2.875 in |
| Rigid/IMC Size | 1.25 in |



*Representative Image

| | |
|------------|----------|
| Trade Size | 3 |
| Weight | 0.14 lb |
| Width | 0.875 in |

Certifications And Compliance

| | |
|----------------------|--------------|
| Certified Listed | cULus Listed |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 100 |
| Pallet Quantity | 4800 |

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195968-1](#)
- [Sales Drawings - 2055 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 2055](#)
- [Terms and Conditions - HCC Terms & Conditions](#)