



#3TS 1-1/4 in. Rigid 1-1/2 in. EMT Threaded Hanger

By Raco
Catalog # 2055TH



#3TS 1-1/4 in. Rigid 1-1/2 in. EMT Threaded Hanger

*Representative Image

Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	3
Material	Steel
Max Load Lbs.	80 lb
UPC	050169911945

Dimensions

Dimensions	1.75 in x 1 in x 3.26 in
EMT Size	1.5 in
Height	3.26 in
Length	1.75 in
Rigid/IMC Size	1.25 in
Trade Size	Rigid/IMC 1-1/4 in, EMT 1-1/2
Weight	0.142 lb
Width	1 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	7200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)
[Terms and Conditions - HCC Terms & Conditions](#)

