



#4TS 1-1/2 in. Rigid Threaded Hanger

By Raco
Catalog # 2056TH

#4TS 1-1/2 in. Rigid Threaded Hanger



*Representative Image

Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	4
Material	Steel
Max Load Lbs.	80 lb
UPC	050169911952

Dimensions

Dimensions	2 in x 1 in x 3.48 in
Height	3.48 in
Length	2 in
Rigid/IMC Size	1.5 in
Trade Size	Rigid/IMC 1-1/2 in
Weight	0.151 lb
Width	1 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	7200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)

[Certifications - UL COC - E195968-3](#)

[Customer Notices - Prop65_Cancer](#)

[SDS - HCC SDS](#)

[Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)

[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2056TH-SPEC-EN | REV 6/2024