



## #5TS 2 in. Rigid/EMT Threaded Hanger

By Raco  
Catalog # 2058TH

#5TS 2 in. Rigid/EMT Threaded Hanger



\*Representative Image

### Features

- Hangers are supplied with a retained bold and threaded hole eliminating the need for a nut
- The design allows for quick and easy installation using a screwdriver or nut driver
- Pregalvanized finish provides corrosion protection
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Hangers
Hanger Size	5
Material	Steel
Max Load Lbs.	100 lb
UPC	050169911969

### Dimensions

Dimensions	2.438 in x 1 in x 3.91 in
EMT Size	2 in
Height	3.91 in
Length	2.438 in
Rigid/IMC Size	2 in
Trade Size	2 in
Weight	0.169 lb
Width	1 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	50
Pallet Quantity	3600

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)

[Customer Notices - Prop65\\_Cancer](#)

[SDS - HCC SDS](#)

[Sell Sheets - Conduit Hangers with Bolt and Threaded Hole](#)

[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-2058TH-SPEC-EN | REV 6/2024