



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 KO's & Five TKO's, Flush, W Bracket

By Raco
Catalog # 208



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 KO's & Five TKO's, Flush, W Bracket

Features

- TKO knockout design provides installation flexibility
- W style bracket, flush
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

General

Bracket Type	W, for Metal or Wood Studs
Catalog Number	208
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169902080
Wiring System	Conduit

Dimensions

Actual Depth	1.75 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	6.688 in
Raised Ground	No
Weight	0.878 lb
Width	5.938 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1500

Product Assets

[3D Product View - RACO_8208](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 208](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-208-SPEC-EN | REV 6/2024