



1-1/2 in. Flex Straight Squeeze Connector, Uninsulated

By Raco
Catalog # 2106

1-1/2 in. Flex Straight Squeeze Connector, Uninsulated



*Representative Image

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Yes
Fitting Type	Connectors
Material	Malleable Iron
UPC	050169021064

Dimensions

Dimensions	2.469 in x 2.42 in x 2.844 in
Height	2.844 in
Length	2.469 in
Trade Size	1-1/2 in
Weight	0.658 lb
Width	2.42 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	3675

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2106-SPEC-EN | REV 6/2024