



# 2 in. Flex Straight Squeeze Connector, Uninsulated

By Raco  
Catalog # 2108

2 in. Flex Straight Squeeze Connector, Uninsulated

## Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

## General

Catalog Number	2108
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Yes
Fitting Type	Connectors
Item Type	4d
Material	Malleable Iron
UPC	050169021088

## Dimensions

Dimensions	2.75 in x 3.04 in x 3.344 in
------------	------------------------------



\*Representative Image

Height	3.344 in
Length	2.75 in
Trade Size	2 in
Weight	0.959 lb
Width	3.04 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer cULus Listed
--	--------------------------------------

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3000

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[SDS - HCC SDS](#)  
[Specifications - 2108](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand