



## 4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps, Five 1/2 in. KO's and Two TKO's

By Raco  
Catalog # 211

4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps, Five 1/2 in. KO's and Two TKO's



### Features

- Welded steel construction with nonmetallic sheathed cable clamps
- 4 in. square x 1-1/2 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with five 1/2 in. and two 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 21.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169902110
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Actual Depth	1.563 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	No
Weight	0.771 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2500

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-211-SPEC-EN | REV 6/2024