



3 in. Flex Straight Squeeze Connector, Uninsulated

By Raco
Catalog # 2112

3 in. Flex Straight Squeeze Connector, Uninsulated



*Representative Image

Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Catalog Number	2112
Conduit Type	Flexible Metal Conduit
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Item Type	4D
Material	Malleable Iron
UPC	050169021125

Dimensions

Dimensions	3.234 in x 4.3 in x 5 in
Height	5 in
Length	3.234 in
Trade Size	3 in
Weight	2.026 lb
Width	4.3 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1080

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2112-SPEC-EN | REV 6/2024