



## 3 in. EMT Set-Screw Connector, Uninsulated

By Raco  
Catalog # 2142

3 in. EMT Set-Screw Connector, Uninsulated



\*Representative Image

### Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.
- 2 set-screw

### General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Item Type	4D
Material	Steel
UPC	050169021422

### Dimensions

Dimensions	3.125 in x 4.375 in x 4.55 in
Height	4.55 in
Length	3.125 in
Trade Size	3 in
Weight	1.55 lb
Width	4.375 in

### Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	1
Pallet Quantity	648

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195970 - 1](#)  
[Certifications - UL COC - E195969- 1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2142-SPEC-EN | REV 6/2024