



4 in. EMT Set-Screw Connector, Uninsulated

By Raco
Catalog # 2146

4 in. EMT Set-Screw Connector, Uninsulated



*Representative Image

Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Tri-head screws may be installed using slotted, Phillips, or Robertson head screwdriver
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.
- 2 set-screw

General

Conduit Type	EMT
Connector Type	Set-Screw
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Item Type	4D
Material	Steel
UPC	050169021460

Dimensions

Dimensions	4.5 in x 5.4 in x 5.8 in
Height	5.8 in
Length	4.5 in
Trade Size	4 in
Weight	2.3 lb
Width	5.4 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	1
Pallet Quantity	448

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195970 - 1](#)
[Certifications - UL COC - E195969- 1](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2146-SPEC-EN | REV 6/2024