



3/8 in. Flex/AC 90 Degree Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco
Catalog # 2201



3/8 in. Flex/AC 90 Degree Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

General

Catalog Number	2201
Conduit Type	<ul style="list-style-type: none">• Flexible Metal Conduit• Armored Cable/Metal Clad (AC/MC)
Connector Type	Squeeze
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022016

Dimensions

Dimensions	2.016 in x 1.375 in x 1.32 in
------------	-------------------------------

Height	1.32 in
Length	2.016 in
Trade Size	3/8 in
Weight	0.087 lb
Width	1.375 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer cULus Listed
---	-----------------------------------

Logistics

Carton Quantity	50
Pallet Quantity	20250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - MC_BX_CONDUIT LOGO](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)