



2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco
Catalog # 2208



*Representative Image

2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable.

Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

General

Conduit Type	<ul style="list-style-type: none">• Flexible Metal Conduit• Armored Cable/Metal Clad (AC/MC)
Connector Type	Squeeze
EU RoHS Indicator	Yes
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022085

Dimensions

Dimensions	6.797 in x 3.797 in x 4.53 in
Height	4.53 in
Length	6.797 in
Trade Size	2 in
Weight	3.094 lb
Width	3.797 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	5
Pallet Quantity	600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - MC_BX_CONDUIT LOGO](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2208-SPEC-EN | REV 6/2024