



## 2-1/2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

By Raco  
Catalog # 2210



\*Representative Image

2-1/2 in. 90 Degree Flex Squeeze Connector, Uninsulated, for FMC/AC/MC Cable

### Features

- All malleable construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection

### General

Catalog Number	2210
Conduit Type	<ul style="list-style-type: none"><li>• Flexible Metal Conduit</li><li>• Armored Cable/Metal Clad (AC/MC)</li></ul>
Connector Type	Squeeze
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Malleable Iron
UPC	050169022108

### Dimensions

Dimensions	7.563 in x 4.328 in x 5.25 in
Height	5.25 in
Length	7.563 in
Trade Size	2-1/2 in
Weight	3.616 lb
Width	4.328 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	1
Pallet Quantity	360

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - MC\\_BX\\_CONDUIT LOGO](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-2210-SPEC-EN | REV 6/2024