



## 4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps, Three 1/2 in. KO's and One TKO, FS Bracket, Flush

By Raco  
Catalog # 223



4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps,  
Three 1/2 in. KO's and One TKO, FS Bracket, Flush

### Features

- Welded steel construction with "FS" bracket to mount on flat side of stud and nonmetallic sheathed cable clamps
- 4 in. square x 1-1/2 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with three 1/2 in. and one 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 21.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	FS, for Metal or Wood Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002230
Wiring System	Nonmetallic Sheathed Cable

### Dimensions

Actual Depth	2.087 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	6.956 in
Raised Ground	No
Weight	0.816 lb
Width	4.494 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 3](#)  
[Certifications - UL COC - E195978-18](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - 223](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-223-SPEC-EN | REV 6/2024