



5 in. EMT or Rigid/IMC 2-Hole Strap

By Raco
Catalog # [2245-2](#)

5 in. EMT or Rigid/IMC 2-Hole Strap



*Representative Image

Features

- Stamped steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Not UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps
Material	Steel
UPC	050169224526

Dimensions

Dimensions	10.688 in x 1.25 in x 5.672 in
Height	5.672 in
Length	10.688 in
Trade Size	5 in
Weight	1.64 lb
Width	1.25 in

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	875

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-22452-SPEC-EN | REV 6/2024