




4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps, Three 1/2 in. KO's and One TKO, B Bracket, Flush

By Raco
Catalog # 225



4 in. Square Box, Welded, 1-1/2 in. Deep with NMSC Clamps,
Three 1/2 in. KO's and One TKO, B Bracket, Flush

Features

- Welded steel construction with "B" bracket that face mounts on front edge of wood stud and nonmetallic sheathed cable clamps
- 4 in. square x 1-1/2 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with three 1/2 in. and 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 21.0 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

General

Bracket Type	B, for Wood Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002254
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	1.563 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	No
Weight	0.84 lb
Width	6 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-225-SPEC-EN | REV 6/2024