



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, BOX-LOC® MS Bracket, Flush

By Raco
Catalog # 227



4 in. Square Box, Welded, 1-1/2 in. Deep with Nine 1/2 in. KO's and Five TKO's, BOX-LOC® MS Bracket, Flush

Features

- TKO knockout design provides installation flexibility
- MS style BOX-LOC® flush bracket
- Welded construction
- Nine 1/2 in. knockouts and Five TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- RACO 978
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Setback	0.375
Bracket Type	MS, for Metal Studs
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169002278
Wiring System	Conduit

Dimensions

Actual Depth	1.75 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	4.5 in
Raised Ground	No
Weight	0.834 lb
Width	5.625 in

Electrical Ratings

Power Distribution Features Fire Rated

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 25
Packaging Type No Packaging
Pallet Quantity 1650

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 227](#)
[SDS - HCC SDS](#)
[Sell Sheets - Box Positioning Products](#)
[Sell Sheets - BOX-LOC Metal Stud Bracketed Boxes](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-227-SPEC-EN | REV 6/2024