



1/2 in. Conduit Clamp, Edge Type

By Raco
Catalog # [2302EC](#)

1/2 in. Conduit Clamp, Edge Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

| | |
|-------------------|----------------------|
| Conduit Type | Rigid/IMC |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Clamps |
| Material | Malleable Iron |
| UPC | 050169986028 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 2.18 in x 2.18 in x 2.85 in |
| Height | 2.85 in |
| Length | 2.18 in |
| Trade Size | 1/2 in |
| Weight | 0.773 lb |
| Width | 2.18 in |

Certifications And Compliance

| | |
|------------------|--------------|
| Certified Listed | cULus Listed |
|------------------|--------------|

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |
| Pallet Quantity | 3750 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC_SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-2302EC-SPEC-EN | REV 6/2024