



3/4 in. Conduit Clamp, Edge Type

By Raco
Catalog # 2303EC

3/4 in. Conduit Clamp, Edge Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Catalog Number	2303EC
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986035

Dimensions

Dimensions	2.325 in x 2.18 in x 3 in
------------	---------------------------

Height	3 in
Length	2.325 in
Trade Size	3/4 in
Weight	0.806 lb
Width	2.18 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	25
Minimum Pack Quantity	25

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Specifications - 2303EC](#)
[Terms and Conditions - HCC Terms & Conditions](#)