



## 2 in. Conduit Clamp, Edge Type

By Raco  
Catalog # [2308EC](#)

2 in. Conduit Clamp, Edge Type



\*Representative Image

### Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

### General

|                   |                      |
|-------------------|----------------------|
| Catalog Number    | 2308EC               |
| Conduit Type      | Rigid/IMC            |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type      | Clamps               |
| Material          | Malleable Iron       |
| UPC               | 050169986073         |

### Dimensions

|            |                           |
|------------|---------------------------|
| Dimensions | 4.05 in x 2.5 in x 4.4 in |
| Height     | 4.4 in                    |

|            |          |
|------------|----------|
| Length     | 4.05 in  |
| Trade Size | 2 in     |
| Weight     | 1.752 lb |
| Width      | 2.5 in   |

### Certifications And Compliance

|                          |                      |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| Certified Listed         | cULus Listed         |

### Logistics

|                       |      |
|-----------------------|------|
| Carton Quantity       | 25   |
| Minimum Pack Quantity | 25   |
| Pallet Quantity       | 1600 |

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC - E195968-3](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® Conduit Clamps](#)  
[Specifications - 2308EC](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand