



2-1/2 in. Conduit Clamp, Edge Type

By Raco
Catalog # [2310EC](#)

2-1/2 in. Conduit Clamp, Edge Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986080

Dimensions

Dimensions	4.65 in x 3 in x 5 in
Height	5 in
Length	4.65 in
Trade Size	2-1/2 in
Weight	2.069 lb
Width	3 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	1600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2310EC-SPEC-EN | REV 6/2024