



## 3 in. Conduit Clamp, Edge Type

By Raco  
Catalog # 2312EC

3 in. Conduit Clamp, Edge Type



\*Representative Image

### Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986097

### Dimensions

Dimensions	5.3 in x 3 in x 5.6 in
Height	5.6 in
Length	5.3 in
Trade Size	3 in
Weight	2.46 lb
Width	3 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	750

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195968-3](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® Conduit Clamps](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand