



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground

By Raco
Catalog # [232](#)



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground

Features

- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in KO's & Six TKO's
- UL Listed
- 30.3 cu. in. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls

General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	<ul style="list-style-type: none">• Box• Box
UPC	050169902325
Wiring System	Conduit

Dimensions

Actual Depth	2.434 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	Yes
Weight	0.898 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1750

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-5](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-232-SPEC-EN | REV 6/2024