



1/2 in. Conduit Clamp, Parallel Type

By Raco
Catalog # 2322PC

1/2 in. Conduit Clamp, Parallel Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986103

Dimensions

Dimensions	2.85 in x 1.175 in x 1.438 in
Height	1.438 in
Length	2.85 in
Trade Size	1/2 in
Weight	0.538 lb
Width	1.175 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	50
Pallet Quantity	4000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2322PC-SPEC-EN | REV 6/2024