



1 in. Conduit Clamp, Parallel Type

By Raco
Catalog # 2324PC

1 in. Conduit Clamp, Parallel Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986127

Dimensions

Dimensions	3.2 in x 1.29 in x 2 in
Height	2 in
Length	3.2 in
Trade Size	1 in
Weight	0.624 lb
Width	1.29 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	50
Pallet Quantity	4000

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Certifications - UL COC - E195968-3](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - RACO® Conduit Clamps](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-2324PC-SPEC-EN | REV 6/2024