



1 in. Conduit Clamp, Parallel Type

By Raco
Catalog # 2324PC

1 in. Conduit Clamp, Parallel Type



*Representative Image

Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

General

Catalog Number	2324PC
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986127

Dimensions

Dimensions	3.2 in x 1.29 in x 2 in
------------	-------------------------

Height	2 in
Length	3.2 in
Trade Size	1 in
Weight	0.624 lb
Width	1.29 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195968-3](#)
[SDS - HCC SDS](#)
[Sell Sheets - RACO® Conduit Clamps](#)
[Specifications - 2324PC](#)
[Terms and Conditions - HCC Terms & Conditions](#)