



## 2 in. Conduit Clamp, Parallel Type

By Raco  
Catalog # 2328PC

2 in. Conduit Clamp, Parallel Type



\*Representative Image

### Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986158

### Dimensions

Dimensions	4.325 in x 1.78 in x 2.875 in
Height	2.875 in
Length	4.325 in
Trade Size	2 in
Weight	0.996 lb
Width	1.78 in

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195968-3](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® Conduit Clamps](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand