



## 4 in. Square Box, Welded with Elevated Conduit KO's, 2-1/8 in. Deep, 600V, Elevated Side Knockouts, Raised Ground

By Raco  
Catalog # [232CS](#)



4 in. Square Box, Welded with Elevated Conduit KO's, 2-1/8 in. Deep, 600V, Elevated Side Knockouts, Raised Ground

### Features

- Welded steel construction
- 4 in. square x 2-1/8 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Elevated Knockouts on two sides help to eliminate the need for bends or offsets by allowing the conduit runs to enter straight into the box
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169932322

### Dimensions

Actual Depth	2.188 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	Yes
Weight	0.898 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	1750

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 2](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - 232CS](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - 4 in. Square Box with Elevated Knockouts for Corrugated Steel Walls](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-232CS-SPEC-EN | REV 6/2024