



ULTIMATE G SERIES MOUNTING BRACKET WITH 4 IN STAB-It(r) BOX

By Raco
Catalog # 232GSCM



ULTIMATE G SERIES MOUNTING BRACKET WITH 4 IN STAB-It(r) BOX

Features

- Works with any depth 4" and 4-11/16" boxes
- RACO's built in STAB-iT connectors are the fastest way to terminate MC cable
- Works with any 4" or 4-11/16" mud ring
- ProReady solutions offer installation flexibility, saving time and labor
- Clips to stud or open center bracket for hands-free installation
- Gangable, making it easy to add more boxes
- Mounts to stud or 9030G open center bracket
- Contractor can decide how to use it at the job site

Application

Ideal for prefab, RACO Ultimate G series brackets work with any box 4" or 4-11/16" box and mud rings, mount to studs or 9030 G open center bracket

General

Catalog Number 232GSCM
UPC 050169985502

Dimensions

Cubic Capacity 133.781608 cu.in
Depth 2.84 in
Height 6.34 in
Width 7.43 in

Logistics

Carton Quantity 12
Pallet Quantity 540

Product Assets

[Brochures - PRO READY® Ultimate G Series Mounting Brackets](#)
[Catalogs - Steel Boxes, Covers and Accessories](#)
[Sales Drawings - 232GSCM Customer Drawing](#)
[Specifications - 232GSCM](#)