



Stab-iT® 4" Electrical Box

By Raco
Catalog # [232MSHF](#)

4 in. Square Box, Welded with STAB-IT® Connector, 2-1/8 in. Deep, 600V, Raised Ground, 8 in. #12 Solid Copper Pigtail, Heavy Duty Universal Bracket Support, M Bracket,



Features

- Welded steel construction with "UBS" support with preset bend points to work with wall thickness 2-1/2 to 6 in., "M" brackets on both sides of the box, STAB-IT® connector and cable management clip
- 4 in. square x 2-1/8 in. deep
- Designed for quick installation of flex, MC, MCI, MCI-A, AC, and HCF Cable
- TKO® Knockouts allows for design and installatin flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground pigtail
- Acceptable for use in 2-hour fire rated walls

Application

Commercial

General

Bracket Type	M, for Metal or Wood Studs
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts - Bottom	(1) 1/2", (1) 1/2"-3/4" TKO
Knockouts - Side	(6) 1/2" (3) 1/2"-3/4" TKO
Number of Gang(s)	2-Gang
UPC	050169992845

Dimensions

Raised Ground	Yes
---------------	-----

Certifications and Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Pallet Quantity	1375

Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)
[Brochures - STAB-iT® Electrical Boxes](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Installation Manuals - 119030_RA-356 Instr for web](#)
[Video - RACO: STAB-IT® vs competition](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-232MSHF-SPEC-EN | REV 1/2024