



## 4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in. KO's & Five TKO's, Raised Ground, Old-Work

By Raco  
Catalog # [232-OW](#)



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in. KO's & Five TKO's, Raised Ground, Old-Work

### Features

- Use in old work applications with mounting bracket
- Combination screw heads allow quick installation
- Welded construction
- Eight 1/2 in. knockouts and four TKO knockouts
- UL Listed
- 30.3 cu. in. capacity
- Raised ground; 4 in. Mounting bracket
- Acceptable in 2-hour fire rated walls
- UPC barcoded

### General

Bracket Type	No Bracket
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169502327
Wiring System	Conduit

### Dimensions

Actual Depth	2.48 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4.75 in
Raised Ground	Yes
Weight	1.12 lb
Width	4.88 in

### Certifications And Compliance

Certified Listed	UL Listed
ENERGY STAR Certified	Yes

### Logistics

Carton Quantity	25
Pallet Quantity	1375

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 2](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - 232-OW](#)  
[Sales Drawings - RACO-welded-steel-box-infographic](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - Service Truck Solutions](#)  
[Sell Sheets - RETRO-RING® Life Safety Appliances](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-232OW-SPEC-EN | REV 6/2024