



## 4 in. Square Box, Welded with STAB-IT® Connector, 2-1/8 in. Deep, Raised Ground, Solid Copper Pigtail, Cable Mgmt Clip

By Raco  
Catalog # 232SCM



4 in. Square Box, Welded with STAB-IT® Connector, 2-1/8 in. Deep, Raised Ground, 8 in. #12 Solid Copper Pigtail, Cable Management Clip

### Features

- Welded steel construction with STAB-IT® connector and cable management clip
- 4 in. square x 2-1/8 in. deep
- TKO® Knockouts allow for design and installation flexibility
- Supplied with seven 1/2 in. and four 1/2-3/4 in. TKO® knockouts
- Combination Phillips/slotted screw heads
- 30.3 cu. in. capacity
- Includes 8 in. #12 solid copper ground pigtail
- Acceptable for use in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Catalog Number	232SCM
Color	Gray
Drawn or Welded	Welded
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169892329

### Dimensions

Actual Depth	2.2 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in
Weight	1.052 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Pallet Quantity	1750

### Product Assets

[3D Models - 232SCM-3D](#)  
[Brochures - STAB-iT® Electrical Boxes](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-5](#)  
[Certifications - UL COC - E195978- 2](#)  
[Product Logo - STAB-IT](#)  
[Sales Drawings - 232SCM Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® STAB-IT](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - RACO: STAB-IT® with Cable Management](#)  
[Video - RACO: STAB-IT® vs competition](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-232SCM-SPEC-EN | REV 6/2024