



## 4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground, 8 in. #12 Solid Copper Pigtail

By Raco  
Catalog # 232SLD



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground, 8 in. #12 Solid Copper Pigtail

### Features

4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground, 8 in. #12 Solid Copper Pigtail

### General

Bracket Type	No Bracket
Catalog Number	232SLD
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169995143

### Dimensions

Actual Depth	2.438 in
Depth	2.125 in
Height	4 in
Raised Ground	Yes

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Logistics

Carton Quantity	25
Pallet Quantity	1750

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978- 2](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - 232SLD Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-232SLD-SPEC-EN | REV 6/2024