




4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground, 10 in. #12 Stranded Copper Pigtail

By Raco
Catalog # 232SM



4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground, 10 in. #12 Stranded Copper Pigtail

Features

- Combination screw heads allow quick installation
- Welded construction
- Eight 1/2 in. knockouts and four TKO knockouts
- 30.3 cu. in. capacity
- Raised ground, 10 in. #12 stranded copper pigtail
- Acceptable in 2-hour fire rated walls
- UPC barcoded

General

Bracket Type	No Bracket
Catalog Number	232SM
Color	Gray
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Number of Gang(s)	2-Gang
Type	Box
UPC	050169982327
Wiring System	Conduit

Dimensions

Actual Depth	2.438 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	Yes
Weight	0.947 lb
Width	4 in

Certifications And Compliance

Certified Listed cULus Listed

Logistics

Carton Quantity	25
Pallet Quantity	1750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - 232SM](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-232SM-SPEC-EN | REV 6/2024