



# 2-1/2 in. Conduit Clamp, Parallel Type

By Raco  
Catalog # 2330PC

2-1/2 in. Conduit Clamp, Parallel Type



\*Representative Image

## Features

- Three available styles, Parallel, Edge and Right Angle, to meet every installation need
- Heavy duty U-bolts, hex bolts and hex nuts
- Capable of supporting heavy loads
- Hot dipped galvanized malleable iron construction provides excellent weatherability and corrosion protection
- Perfect for commercial construction applications
- Additional sizes available

## General

Catalog Number	2330PC
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Clamps
Material	Malleable Iron
UPC	050169986165

## Dimensions

Dimensions	5.21 in x 1.79 in x 3.25 in
Height	3.25 in

Length	5.21 in
Trade Size	2-1/2 in
Weight	1.304 lb
Width	1.79 in

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus Listed

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2000

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC - E195968-3](#)  
[SDS - HCC SDS](#)  
[Sell Sheets - RACO® Conduit Clamps](#)  
[Specifications - 2330PC](#)  
[Terms and Conditions - HCC Terms & Conditions](#)